











Ref: 6953156301603

ANLAN face massager 01-ADRY32-02A

ANLAN face massager 01-ADRY32-02A

ANLAN facial massager 01-ADRY32-02A

ANLAN 01-ADRY32-02A massager is a device tailored to the needs of your skin. The product allows you to thoroughly cleanse your face and prepare it for further skin care steps. Moreover, it aids the absorption of nutrients, reduces the appearance of wrinkles and dark circles around the eyes. It also helps restore firmness and radiance to the skin.

Cleansing facial skin

Proper facial care begins with cleansing. Clean mode uses heat therapy ($38^{\circ}\text{C} \sim 42^{\circ}\text{C}$) to open pores. Vibrations of about 10,000 rpm effectively remove impurities and makeup residue, while positive ions facilitate deep pore cleansing.

Moisture mode

Choose Moist mode, which helps moisturize the skin. The high vibration frequency breaks down macromolecules in skin care products. What's more, negative ions help the absorption of nutrients from cosmetics. Enjoy healthy and moisturized skin with ANLAN 01-ADRY32-02A.

Restore skin firmness and get rid of wrinkles

Give your skin a youthful appearance. The ANLAN 01-ADRY32-02A massager offers an EMS mode that tightens the skin and provides a

Mobilemax - Gadgets and Accessories Rua Vasco da Gama n61, 8005-411, Estoi - Faro, Portugal (Continente) Phone: +351962484153
(Call to national mobile network)
Email: info@mobilemax.pt



lifting effect. Eye mode, on the other hand, uses microcurrents and 3 levels of warm compression to soothe the delicate skin around the eyes and facilitate the absorption of cosmetics. Moreover, it tightens the skin, reduces the appearance of wrinkles and reduces dark circles under the eyes.

Light therapy

Experience the beneficial power of phototherapy. The massager uses blue light with a wavelength of 463 nm, which fights bacterial conditions and helps treat acne. And red light (623 nm) stimulates collagen production, improves skin elasticity and slows down the aging process.

User-friendly

Operating the device will not cause you any problems. You can also use the power button to change modes, and a dedicated button allows you to adjust the temperature and EMS level. What's more, the easy-to-read LCD display informs you about the set mode. In addition, the massager does not take up much space in your bathroom or vanity case, making it easy to transport and store.

Included

massagerholder for a cosmetic padUSB-A to USB-C charging cableinstruction manual

ManufacturerANLANModel01-ADRY32-02AColorwhiteMaterialABSDimensions170 \times 55 \times 56 mmWeightapprox. 115 gVibration frequencyapprox. 10,000 rpmTemperatureapprox. 38°C \sim 42°CLight wavelengthRed: approx. 623 nm, blue: approx. 463 nmBattery capacity450 mAhCharging timeapprox. 2.5 hAutomatic shutdownafter approx. 5 min of non-use

Price:

€ 33.00

Phone: +351962484153

Email: info@mobilemax.pt

(Call to national mobile network)

Health and beauty, Facial care devices, Massagers